



-INSTRUCTION MANUAL-
取扱説明書

RETRACTOR
TOOL BALANCER



※ 제품규격 (SPECIFICATION)仕様

Model 形式	CAPACITY 容量		WIRE TRAVEL ストローク		WEIGHT 質量	
	kg	lb	m	ft	kg	lb
(N)TW-06R	0.2~0.6	0.4~1.3	1.5	4.9	0.3	0.7
(N)TW-1R	0.5~1.5	1.1~3.3	1.5	4.9	0.3	0.7
(N)TW-2R	1.0~2.0	2.2~4.4	1.5	4.9	0.3	0.7

* (N) : 수출사양 (Export Specification) 輸出仕様

※ 부품일람표(PART LIST)

No.	부품명(Part Name) 部品名	No.	부품명(Part Name) 部品名
1	주행거(MAIN HANGER)메인한가ー	6	심블(THIMBLE)シンプル
2	보조행거(SECONDARY HANGER)補助한가ー	7	후크(HOOK)フック
3	케이스커버(CASE COVER)케이스카버	8	핸들(HANDLE)ハンドル
4	완충고무(SHOCK ABSORBER)쇼크아브소ー버	9	케이스(CASE)ケース
5	고무장치(STOPPER)스톱퍼	10	와이어(WIRE)ワイヤーロープ

1. OPERATION INSTRUCTION

- (1) Both the ①Main Hanger and the ②Secondary Hanger should be used together to hold this product.
- (2) Adjustment of the vertical displacement of wire : By using ⑤Stopper of this product, the length of vertical travel of ⑩Wire can be adjusted to suitable working environment.

■ ADJUSTMENT PROCEDURE

1. Separate the ④Shock Absorber from ⑤Stopper.
 2. Loosen the bolts on the ⑤Stopper, and shift the ⑤Stopper to the suitable position on the ⑩Wire.
 3. Tighten the bolts and nuts securely.
 4. Insert the ④Shock Absorber into the ⑤Stopper.
- (3) Spring tension adjustment : Turn the ⑧Handle clockwise or counter clockwise to adjust spring tension. Make sure the tension is appropriate for the loaded weight.

■ ADJUSTMENT PROCEDURE

- To increase the tension : Turn the ⑧Handle clockwise.
- To decrease the tension : Turn the ⑧Handle counter-clockwise while pulling the ⑧Handle.

2. CAUTION

- (1) Make sure to hang this product with ②Secondary Hanger.
- (2) Check if the weight of loading tool is appropriate to this product before putting it to use.
- (3) When adjusting the spring tension, remove the loaded tool from the ⑩Wire before operating the ⑧Handle.
- (4) Check all the bolts and nuts on ⑤Stopper are tightened securely.
- (5) Do not push the ⑩Wire into this product by force. It may cause the ⑩Wire to separate from the product.

3. INQUIRIES FOR PURCHASING OR HANDLING

For the information of performance, quality or handling of this product, please contact our agent or Head Office.
We will answer to your inquiries sincerely.

Manufacturer

MiJiN system Co.,LTD.

53-1, JEIL-RI, YANGJI-MYUN, CHEOIN-GU,
YONGIN-CITY, KYONGGI-DO, KOREA
TELE: 82-31-335-8787 / FAX: 82-31-336-0821